




RSQ-SERIES




Standard Rotation Stages. 360 degrees coarse adjustment and fine adjustment within 10 degrees. The thinner body design can be used in the lower beam height systems.

ITEM	PLATFORM SIZE	ACTUATORS	AXIS OF TRAVEL	ECCENTRICITY	COARSE ADJUSTMENT	FINE ADJUSTMENT	RESOLUTION	MICROMETER ACCURACY	WEIGHT
RSQ-38A	Φ 38.0mm	100TPI	Θ	25um	360°	0.1°	0.5°	NA	
RSQ-59	Φ 59.0mm	Micrometer	Θ	25um	360°	5°	NA	0.02°	
RAQ-59A	Φ 59.0mm	100TPI	Θ	25um	360°	5°	0.4°	NA	

RSQ-38A



RSQ-59



RSQ-59A

